

[See all 3 Products in Family](#)

Adjustable Grating Mount Adapter for 40-60mm Optic



[+1](#)

Stock **#18-539** **7 In Stock**

-

1

+

S\$282⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	S\$282.80 each
Qty 10+	S\$268.80 each
Need More?	Request Quote

Product Downloads

General	
Fixed	Type:
Square or Rectangular	Type of Optics:
Includes Hex Wrench for Locking Screws	Note:
Compatible Kinematic Mount:	

Threading & Mounting

Size of Compatible Optics (mm):
40.0 - 60.0

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 247:
Compliant

Product Details

- Mount up to 60mm Tall Diffraction Gratings
- Easy Adjustment via Side Locking Screws
- Designed for Integration into 25.4mm Diameter Optic Mounts

Adjustable Grating Mounts are designed to hold diffraction gratings without damaging their sensitive grating surface. Featuring a 3-point mounting style with spring and metal contacts, these mounts provide adequate clamping pressure while allowing for easy adjustment via side locking screws. A 25.4mm diameter extension on the rear of the mount allows for integration into [TECHSPEC® Kinematic Mounts](#), [E-Series Circular Kinematic Mounts](#), and [fixed mirror mounts](#). Adjustable Grating Mounts can be adjusted to accommodate a range of grating sizes, up to 60mm in height.