

Hi-Res 6.0mm Lens, PAL, Color DSP Board Level Camera



Stock **#57-251** CLEARANCE 3-5 DAYS

− 1 +

S\$144.93

ADD TO CART

Qty 1+

S\$144.93

Volume Pricing

[Request Quote](#)

Get Product Downloads

Video Output:
Analog

Type:
Color Camera

Mounting Threads:
No Mounting Threads/Tripod Adapter

Working Distance (mm):
250 - ∞

Image Buffer:
Not Specified

Type of Sensor: Interlaced CCD
Camera Sensor Format: 1/4"
Resolution (MegaPixels): 0.40
Pixels (H x V): 752 x 582
Exposure Time: 1/60 - 1/100,000s
Connector: Analog, 10" Wire Leads
Power Supply: Separate Power Supply #62-941
GPIOs: N/A
Dimensions (mm): 20 x 32 x 32 (excludes lens mount)
Weight (g): 30
Mount: Lens Included
Housing: Board Level
Interface Port Orientation: Front/Back Panel
Operating Temperature (°C): -10 to +50
Storage Temperature (°C): -20 to +60
Power Requirement: 12 VDC, 130 mA
Signal Format: PAL, Y-C

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View