

# Hoya B390 (UV-VIS) 25.4mm Dia., 1mm Thick, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#18-782** 3-5 DAYS

[Additional Bandwidths](#)

- 1 +

**S\$91.35**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| S\$91.35                      |
| Qty 11+                       |
| S\$81.20                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
25.40

Center Wavelength CWL (nm):

|                                                             |
|-------------------------------------------------------------|
| 390.00                                                      |
| <b>Density (g/cm³):</b><br>2.57                             |
| <b>Full Width-Half Max FWHM (nm):</b><br>125.00             |
| <b>Glass/Filter Number:</b><br><a href="#">Hoya B390</a>    |
| <b>Substrate:</b> <input type="checkbox"/><br>Colored Glass |
| <b>Coating:</b><br>Uncoated                                 |
| <b>Color:</b><br>Blue-Violet                                |
| <b>Surface Quality:</b><br>60-40                            |
| <b>Thickness (mm):</b><br>1.00                              |
| <b>Thickness Tolerance (mm):</b><br>±0.1                    |
| <b>Type:</b><br>Bandpass Filter                             |
| <b>Wavelength:</b><br>UV-Vis                                |
| <b>Parallelism (arcmin):</b><br>≤2                          |
| <b>Dimensional Tolerance (mm):</b><br>±0.2                  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |