

Hoya IR85N (850nm), 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-903 3-5 DAYS

- 1 + **S\$46.40**

ADD TO CART

Qty 1-10
S\$46.40
Qty 11+
S\$40.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Cut-On Wavelength (nm):
850.00 ±10

Density (g/cm³):
490

Glass/Filter Number: Hoya IR85N
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Transformation Temperature (°C): 3.02
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.91
Bevel: Protective as needed
Δλ (nm): <60
TH (%): N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View