

Hoya R64 (640nm), 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-879 3-5 DAYS



1



S\$46.40

ADD TO CART

Qty 1-10

S\$46.40

Qty 11+

S\$40.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50

Cut-On Wavelength (nm):
640.00 ±5

Density (g/cm³):
2.68

Glass/Filter Number: Hoya R64
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Red
Surface Quality: 60-40
Transformation Temperature (°C): 555
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <35
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View