

# Hoya R64 (640nm), 50mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-883 3-5 DAYS

-

1

+

S\$127.60

ADD TO CART

Qty 1-10

S\$127.60

Qty 11+

S\$113.10

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):  
50.00

Cut-On Wavelength (nm):  
640.00 ±5

Density (g/cm³):  
2.68

|                                                             |
|-------------------------------------------------------------|
| <b>Glass/Filter Number:</b><br><a href="#">Hoya R64</a>     |
| <b>Substrate:</b> <input type="checkbox"/><br>Colored Glass |
| <b>Coating:</b><br>Uncoated                                 |
| <b>Color:</b><br>Red                                        |
| <b>Surface Quality:</b><br>60-40                            |
| <b>Transformation Temperature (°C):</b><br>555              |
| <b>Thickness (mm):</b><br>1.00                              |
| <b>Thickness Tolerance (mm):</b><br>±0.1                    |
| <b>Type:</b><br>Longpass Filter                             |
| <b>Wavelength:</b><br>VIS                                   |
| <b>Dimensional Tolerance (mm):</b><br>±0.2                  |
| <b>Reflection Factor P<sub>d</sub>:</b><br>0.92             |
| <b>Bevel:</b><br>Protective as needed                       |
| <b>Δλ (nm):</b><br><35                                      |
| <b>TH (%):</b><br>>85                                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |