

Hoya RM100 (1000nm), 50mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-915 3-5 DAYS

- 1 + **S\$127.60**

ADD TO CART

Qty 1-10

S\$127.60

Qty 11+

S\$113.10

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00

Cut-On Wavelength (nm):
1,000.00

Density (g/cm³):
450

Glass/Filter Number: Hoya RM100
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Transformation Temperature (°C): 3.23
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: N/A
Bevel: Protective as needed
Δλ (nm): N/A
TH (%): N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View