

Hoya UV28N (280nm), 50mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-796 3-5 DAYS

- 1 + **S\$127.60**

ADD TO CART

Qty 1-10
S\$127.60
Qty 11+
S\$113.10
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00

Cut-On Wavelength (nm):
280.00 ±7

Density (g/cm³):
2.61

Glass/Filter Number: Hoya UV28N
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Clear
Surface Quality: 60-40
Transformation Temperature (°C): 572
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <45
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View