

Hoya UV30N (300nm), 50.8mm Sq., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-805 3-5 DAYS

-

1

+

S\$127.60

ADD TO CART

Qty 1-10

S\$127.60

Qty 11+

S\$113.10

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
50.8 x 50.8

Cut-On Wavelength (nm):
300.00 ±7

Density (g/cm³):
2.50

Glass/Filter Number: Hoya UV30N
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Clear
Surface Quality: 60-40
Transformation Temperature (°C): 533
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <40
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View