

[See all 66 Products in Family](#)

IDS GV-5000FA-P-GL, GigE, 1.1" Monochrome Camera POL

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ FAIP65/67 PoE Cameras (Front)



Stock #26-286 **1 In Stock**

- 1 + **\$5,992⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	\$5,992.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Monochrome (Polarized)

Spectrum:

General

Mono POL

Type:

GV-5000FA-P-GL **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ FA **Camera Series:**

Physical & Mechanical Properties

41 x 53 x 42.7 (excludes connectors and lens mount) **Dimensions (mm):**

173 **Weight (g):**

Full **Housing:**

Sensor

128MB **Image Buffer:**

1.1" **Sensor Format:**

12.29 **Resolution (Megapixels):**

10.00 **Frame Rate (fps):**

4,104 x 3,006 **Pixels (H x V):**

3.45 x 3.45 **Pixel Size, H x V (µm):**

14.158 x 10.37 **Sensing Area, H x V (mm):**

Sony IMX253 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

12 bit **Pixel Depth:**

0.035ms - 2000ms **Exposure Time:**

70.00 **Dynamic Range (dB):**

GigE Vision **Machine Vision Standard:**

Electrical

2 - 4 **Power Consumption (W):**

Hardware & Interface Connectivity

GigE (PoE) **Interface:**

GigE M12, screwable **Connector:**

Power over Ethernet (PoE) or 12 - 24VDC via GPIO with [#19-692](#) **Power Supply:**

2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground **GPIOs:**

Hardware Trigger (GPIO); Software Trigger **Synchronization:**

Back Panel **Interface Port Orientation:**

8-pin Binder connector (Binder series 712: 09-0427-020-08) **GPIO Connector Type:**

Threading & Mounting

C-Mount **Mount:**

1/4-20 with Tripod Mount Adapter [#19-694](#) **Mounting Threads:**

Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

-20 to +60 **Storage Temperature (°C):**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

PRODUCT DETAILS

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.
