

[See all 65 Products in Family](#)

IDS U3-3880LE-M-GL, USB 3.0, 1/1.8" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (C/CS - Mount, Full Housing, Front View)



Stock #24-113 **1 In Stock**

[Similar Cameras](#)

⊖ 1 ⊕ **S\$543²⁰**

ADD TO CART

Volume Pricing

Qty 1+	S\$543.20 each
Need More?	Request Quote

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

U3-3880LE-M-GL **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ LE **Camera Series:**

Physical & Mechanical Properties

47 x 46 x 23.9 (excludes connectors and lens mount) **Dimensions (mm):**

36 **Weight (g):**

Full **Housing:**

Sensor

Not Specified **Image Buffer:**

1/1.8" **Sensor Format:**

6.41 **Resolution (Megapixels):**

54.00 **Frame Rate (fps):**

3,088 x 2,076 **Pixels (H x V):**

2.40 x 2.40 **Pixel Size, H x V (µm):**

7.411 x 4.982 **Sensing Area, H x V (mm):**

Sony IMX178 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Rolling **Shutter Type:**

12 bit **Pixel Depth:**

0.014ms - 1090ms **Exposure Time:**

71.00 **Dynamic Range (dB):**

USB3 Vision **Machine Vision Standard:**

Electrical

1 - 1.5 **Power Consumption (W):**

Hardware & Interface Connectivity

USB 3.0 **Interface:**

USB Type-C **Connector:**

Power over USB **Power Supply:**

N/A **GPIOs:**

Hardware Trigger (GPIO); Software Trigger **Synchronization:**

Back Panel (Right Angle) **Interface Port Orientation:**

No GPIO Connector Available **GPIO Connector Type:**

Threading & Mounting

C/CS-Mount **Mount:**

1/4-20 with Tripod Mount Adapter [#16-017](#) **Mounting Threads:**

Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

-20 to +80 **Storage Temperature (°C):**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

Product Details

- Up to 8.0MP Resolution with Framrates up to 230fps
- Board Level Options with C/CS-Mbunt or S-Mbunt Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GenICam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mbunt or C/CS-Mbunt versions. The C/CS-Mbunt configurations come with a 5mm spacer to easily adapt between C-Mbunt and CS-Mbunt lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.

;