

Infrared Viewer (350-1350nm)



Infrared Viewer (350-1350nm), #36-083



Stock **#36-083** CLEARANCE 3-5 DAYS

− 1 +

S\$2,357.63

ADD TO CART

Qty 1+

S\$2,357.63

Volume Pricing

[Request Quote](#)

Get Product Downloads

Aperture (f/#):
f/1.4 - f/16

Operating Lifetime (hours):
>98-hours continuous

Focal Length FL (mm):
25.00

Magnification:
1:1 (Eyepiece)

Mount: C-Mount
Operating Temperature (°C): -32 to +46
Resolution: 40 lp/mm
Dimensions (inches): 6.5 x 2.1 x 7.5
Spectral Response (nm): 350 - 1350
Weight (g): 595
Working Distance (inches): 7.87 to ∞
Power Requirement: (1) standard "C" cell alkaline battery
Field of View (°): 24
Focus Range: 0.2m - ∞
Filter Thread: M27 x 0.5

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View