

ISO-14524 Reflective Camera Contrast Chart



Stock **#58-944** **1 In Stock**

S\$676^{.20}

ADD TO CART

Volume Pricing

Qty 1-4	S\$676.20 each
Qty 5+	S\$644.00 each
Need More?	Request Quote

Product Downloads

General

NIST Certification:
No

Physical & Mechanical Properties

Length (mm):
395.00

Pattern Size (mm):
200 x 356

Width (mm):
240.00

12

Number of Patches:

31.4 x 31.4

Patch Size (mm):

Optical Properties

Reflective Photo Paper

Substrate:

Optical Density OD (Average):

Background: 0.84

Individual Patches: 0.1, 0.2, 0.31, 0.43, 0.56, 0.70,
0.87, 1.05, 1.27, 1.53, 1.86, 2.30

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 235:

Product Details

- Determines Dynamic Range of Cameras
- 12 gray level patches

The Reflective Contrast Target is designed to determine the range of optical density that an imaging system can capture. This target complies with ISO-14524 specifications.