

JAI 2m Power and GPIO Cable, 6-pin Hirose and Flying Leads



Stock **#29-176** CLEARANCE **1 In Stock**

-

1

+

S\$185^{.15}

ADD TO CART

Volume Pricing	
Qty 1+	S\$185.15 each
Need More?	Request Quote

Product Downloads

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Up to 12.3 MP Resolution
- USB and GigE Versions Available
- Longest Industry Warranty (6 Years)

JAI® Go-X Series Cameras are designed to be compact, industrial grade, reliable cameras with excellent image quality. Featuring industrial grade shock and vibration ratings (80G/10G) as well as excellent thermal dissipation, these cameras are ideal for factory floors and assembly lines. Designed with a variety of capabilities, these cameras are capable of region-of-interest (ROI), blemish compensation with shading correction, and 8, 10, and 12-bit output. JAI®

Go-XSeries Cameras are available in resolutions ranging from 2.3 to 12.3MP with both USB or Gigabit Ethernet (GigE) outputs. Downloadable software is [available](#) for both GigE and USB options.
