

Hoya L37 (370nm), 12.5mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #66-038 3-5 DAYS

⊖ 1 ⊕

S\$46.40

ADD TO CART

Qty 1-10

S\$46.40

Qty 11+

S\$40.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50

Cut-Off Position λ_c (nm):
370±6

Cut-On Wavelength (nm):
370.00 ±6

Density (g/cm³): 3.26
Glass/Filter Number: Hoya L37
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Clear
Surface Quality: 80-50
Transformation Temperature (°C): 440
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.38
Reflection Factor P _d : 0.92
Bevel: Protective as needed
Δλ (nm): <35
TH (%): >85

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View