

Lumenera INFINITY 3-3UR Microscopy Color Camera

See More by [Teledyne DALSA](#)



Stock #33-276 3-5 DAYS

-

1

+

S\$7,141.25

ADD TO CART

Qty 1+
S\$7,141.25
Volume Pricing
Request Quote

Get Product Downloads

Video Output:
USB 3.0

Type:
Color Microscopy Camera

Manufacturer:
Teledyne Lumenera

Mounting Threads:
2 x 1/4-20 (Integrated into Housing)

Image Buffer: Not Specified
Camera Family: INFINITY
Model Number: INFINITY3-3UR
Imaging Sensor: Sony ICX674
Type of Sensor: Progressive Scan CCD
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 2.80
Pixels (H x V): 1,936 x 1,456
Pixel Size, H x V (µm): 4.54 x 4.54
Sensing Area, H x V (mm): 8.79 x 6.61
Frame Rate (fps): 53.00
Pixel Depth: 8/14 bit
Exposure Time: 23µs - 1.3s (video)
Power Supply: Power over USB
Power Consumption (W): 6
GPIOs: N/A
Synchronization: Hardware Trigger (GPIO)
Dimensions (mm): 97.8 x 69.8 x 50.8 (excludes lens mount)
Weight (g): 340
Mount: C-Mount
Housing: Full
Interface Port Orientation: Side Panel
Dynamic Range (dB): 68.8
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +70
GPIO Connector Type: 8-pin Hirose (MRX)

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View