

## M58 x 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock **#36-443** CLEARANCE 3-5 DAYS



1



**S\$31.83**

ADD TO CART

Qty 1+

S\$31.83

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Clear Aperture CA (mm):**  
54.00

**Coating:**  
Uncoated

**Diameter (mm):**  
60.00

**Extinction Ratio:**  
Approx. 19:1 at 400nm  
Approx. 200:1 at 500nm  
≥2700:1 at 550-650nm  
Approx. 600:1 at 700nm

|                                                           |
|-----------------------------------------------------------|
| <b>Filter Thread:</b><br>M58 x0.75                        |
| <b>Substrate:</b> <input type="checkbox"/><br>Float Glass |
| <b>Operating Temperature (°C):</b><br>-15 to +70          |
| <b>Polarization:</b><br>95% Efficiency                    |
| <b>Transmission (%):</b><br>Single: 30<br>Crossed: 0.15   |
| <b>Type:</b><br>Mounted Imaging Filter                    |
| <b>Construction:</b><br>Dichroic                          |
| <b>Mount Thickness (mm):</b><br>8                         |
| <b>Wavelength Range (nm):</b><br>400 - 700                |
| <b>Mount Thickness Including Threads (mm):</b><br>10      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>REACH 201:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |