

M6 x 1.0 Bumper (Package of 4), Sorbothane Bumpers



Stock **#56-923** 20+ In Stock

-

1

+

S\$67^{SS}

ADD TO CART

Volume Pricing	
Qty 1-2	S\$67.55 each
Qty 3+	S\$59.92 each
Need More?	Request Quote

Product Downloads

General	
Metric	Type:
Thread Type: M6	Note:
Physical & Mechanical Properties	
25.40	Thickness (mm):

Sorbothane	Construction:
38.10	Diameter (mm):
30-65 / bumper	Load Capacity (lbs):

Threading & Mounting

12.7	Thread Length (mm):
------	---------------------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 211:
View	Certificate of Conformance:

Product Details

- Absorb and Dissipate Vibration
- Stabilize Equipment up to 152lbs
- English, Metric, or Universal Styles

Sorbothane® Mounts absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (1/4-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® Mounts measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. 1/4-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.