

TECHSPEC® C-Mount, 35mm Sq. x 1mm Thick Plate Mount



Stock #56-264 **10 In Stock**

- 1 + \$408⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	\$408.80 each
Qty 5-9	\$360.78 each
Qty 10-25	\$332.08 each
Need More?	Request Quote

Product Downloads

General

Function:
Optic Mount (Fixed)

Type of Optics:
Square

Note:
Includes one C-Mount Aperture Cap ([#55-245](#))

Dimensions of Compatible Optics (mm):
35.0 Sq.

Physical & Mechanical Properties

38.0 x 38.0 x 50.0 **Dimensions (mm):**

38.0 **Extension Length (mm):**

1.0 **Min. Thickness of Compatible Optics (mm):**

1.0 **Max. Thickness of Compatible Optics (mm):**

Threading & Mounting

C-Mount **Thread Type:**

1/4-20 **Compatible Post:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

Technical Information

