

TECHSPEC[®] C-Mount, 35mm Sq. x 1mm Thick Plate Mount



Stock #56-264 2 In Stock

-

1

+

S\$408^{.80}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$408.80 each
Qty 5-9	S\$360.78 each
Qty 10-25	S\$332.08 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Optic Mount (Fixed)

Function:

Square

Type of Optics:

Note:
Includes one C-Mount Aperture Cap [\(#55-245\)](#)

35.0 Sq.		Dimensions of Compatible Optics (mm):
Physical & Mechanical Properties		
38.0 x 38.0 x 50.0		Dimensions (mm):
38.0		Extension Length (mm):
1.0		Min. Thickness of Compatible Optics (mm):
1.0		Max. Thickness of Compatible Optics (mm):
Threading & Mounting		
C-Mbunt		Thread Type:
1/4-20		Compatible Post:
Regulatory Compliance		
View		Certificate of Conformance:

PRODUCT DETAILS

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
 - Provides a 90° Mounting Interface
 - 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems
- TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mbunt Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mbunt Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.
- Note:** [#11-139](#) and [#11-142](#) each include one S-Mbunt Aperture Cap ([#11-137](#))

TECHNICAL INFORMATION

