

NdGa:YAG Goggle, Narrow Spectrum



Soft Vinyl Goggles

Stock **#58-112** [CONTACT US](#)



1



S\$288.55

ADD TO CART

Qty 1+

S\$288.55

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
Green

Type of Filter:
NdGa:YAG

Optical Density OD (Average):
>9 @ 190-420nm
>5 @ 770-810nm
>10 @ 1064nm
>7 @ 10600 nm
>1 @ 670nm
>7 @ 810-1100nm
>5 @ 9000-1

Type:
Soft Vinyl Goggle

Visible Light Transmission VLT (%):
32.00

EN 207/208 Ratings:
770-810 DIR L5, >810-1100 DL5 + IR L7

Filter Number:
108.00

Filter Material:
Polymer

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)