

Needle Nose Style, Soft Jaw Pliers



Stock **#59-903** **9 In Stock**

-

1

+

S\$64^{.40}

ADD TO CART

Volume Pricing	
Qty 1+	S\$64.40 each
Need More?	Request Quote

Product Downloads

Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

Product Details

- Non-Marring Cushioned Tips
- Screw-In Cushioned Tip Design

- Replacement Tips Available

The slip joint design utilized in these pliers is ideal for handling optics, camera-lens assemblies, and other delicate components. Jaw openings range from 1" to 2.75" (dependent on model). Jaws feature screw-in plastic cushions to protect fine knurling and delicate finishes. Tool body is laminated and handles are covered with rolled vinyl to ensure proper grip.

;