

[See all 10 Products in Family](#)

Nikon 200mm Tube Lens

See More by [Nikon](#)



#58-520: Nikon 200mm Tube Lens

Stock **#58-520** **20+ In Stock**

⊖ 1 ⊕ **S\$840⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	S\$840.00 each
Need More?	Request Quote

Product Downloads

General

Tube Lens **Type:**

Nikon **Manufacturer:**

Physical & Mechanical Properties

29.00 **Length (mm):**

36.0 **Maximum Diameter (mm):**

Optical Properties

200.00	Focal Length FL (mm):
1X	Magnification:
400 - 700	Wavelength Range (nm):
26.5	Field Number (mm):
32.0	Entrance Pupil Diameter (mm):

Threading & Mounting

M38 x 0.5	Mounting Threads:
-----------	--------------------------

Regulatory Compliance


Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Superior UV Transmission
- High Numerical Aperture Designs
- Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

Technical Information



Dimensions (mm)							
Stock No.	Magnification	Parfocal Length	A	B	C	D	
#75-345	4X	60.06	30.0	44.3	19.7	M25 x 0.75	
#88-375	10X	60.06	32.0	58.9	12.0	M25 x 0.75	
#88-376	20X	59.90	33.5	58.9	9.0	M25 x 0.75	
#75-346	40X	60.06	32.0	59.8	8.3	M25 x 0.75	

