

NUV M105 x 1.00 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-604 3-5 DAYS

⊖ 1 ⊕

S\$1,173.05

ADD TO CART

Qty 1-9
S\$1,173.05
Qty 10+
S\$1,114.33
Volume Pricing
Request Quote

Get Product Downloads

Blocking Wavelength Range (nm):
200-250, 400-662

Clear Aperture CA (mm):
100.00

Coating:
Hard Coated

Filter Thread:

M105 x 1.00
Color: NUV
Center Wavelength CWL (nm): 324.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 105.00
Mount Thickness (mm): 5.7
Mount Thickness Including Threads (mm): 8.5
Outer Diameter (mm): 109.80
Substrate Thickness (mm): 1.8
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View