

SCHOTT OG-515, 12.5mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#54-653** 3-5 DAYS

- 1 +

S\$46.40

ADD TO CART

Qty 1-10
S\$46.40
Qty 11+
S\$40.60
Volume Pricing
Request Quote

Get Product Downloads
Diameter (mm): 12.50
Cut-Off Position λ_c (nm): 515±6
Cut-On Wavelength (nm):

515.00
Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT OG515
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 580.00
Spectral Transmittance t_p (%): 93.00
Stopband Limit λ_s (nm): 440.00
Surface Quality: 80-50
Transformation Temperature (°C): 509.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View