

[See all 14 Products in Family](#)

Olympus Wide Field Tube Lens, 180mm Focal Length

See More by [Olympus](#)



Olympus Wide Field Tube Lens, #36-401

Stock **#36-401** **14 In Stock**

⊖ 1 ⊕ **\$861⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	\$861.00 each
Need More?	Request Quote

Product Downloads

General

N5696600 **Model Number:**

Tube Lens **Type:**

Olympus **Manufacturer:**

Optical Properties

180.00 **Focal Length FL (mm):**

1X	Magnification:
400 - 1000	Wavelength Range (nm):
26.5	Field Number (mm):
36.0	Entrance Pupil Diameter (mm):

Threading & Mounting

M41 x0.5	Mounting Threads:
----------	--------------------------

Regulatory Compliance


Exempt	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Ideal for Brightfield, Darkfield, DIC, Fluorescence, or Polarization Microscopy
- Excellent Transmission in the UV
- High Numerical Apertures, Oil Immersion, and Variable Iris Options Available
- Additional [Olympus Infinity Corrected Objectives](#) Available

Olympus Plan Fluorite Objectives are multi-purpose objectives that utilize advanced multi-coatings to provide excellent flat field images from the UV to NIR. The objectives offer high signal-to-noise ratios, excellent resolution, and high contrast imaging capability. These objectives are ideal for brightfield microscopy or Nomarski differential interference contrast (DIC) observations, in addition to darkfield or fluorescence microscopy, or specific polarization techniques. Olympus Plan Fluorite Objectives are available in 4X up to 100X magnification. High Numerical Apertures, Oil Immersion, and Variable Iris options are available. Variable Iris options feature a correction collar to adjust the iris and reduce straylight to fine-tune the image as needed. Additional [Olympus Infinity Corrected Objectives](#) are also offered.

Technical Information



	Stock #	A	B	C	D	E	F	G
UPLFLN 4X	86-817	27.9	2.8	0.0	18.0	18.0	24.0	4.5
UPLFLN 10X	86-818	34.9	10.1	0.0	13.6	13.6	24.0	4.5
UPLFLN 20X	86-819	42.8	5.3	2.3	9.4	15.8	26.0	4.5
UPLFLN 40X	86-820	44.4	5.1	4.0	8.5	16.0	26.0	4.5
UPLFLN 60X	86-822	44.7	5.2	2.7	8.6	17.0	29.0	4.7
UPLFLN 100X(Oil Immersion)	86-823	44.7	5.5	3.0	7.0	17.2	28.0	4.5

