

[See all 66 Products in Family](#)

## Power Supply + 8-pin GPIO Y-cable, IP65/67, 5m/1.8m

See More by [IDS Imaging Development Systems](#)



#19-692: Power Supply + 8-pin GPIO Y-cable, IP65/67, 5m/1.8m

Stock **#19-692** CLEARANCE **3 In Stock**

S\$211<sup>33</sup>

ADD TO CART

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | S\$211.33 each                |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

Camera Accessory **Type:**

**Note:**  
8-pin Binder Connector to open end, 2 branches:  
one branch 6 wires for Trigger and Flash (5m), one  
branch to Power Supply adapter (1.8m)

### Hardware & Interface Connectivity

Length of Cable (m):  
5, 1.8

8-pin Binder Connector

Connector:

---

## Regulatory Compliance

[View](#)

Certificate of Conformance:

[Compliant](#)

REACH 241:

---

## Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.

---

;