

[See all 43 Products in Family](#)

## Power Supply for 10mW HeNe Laser, AC, Bare Wire Leads



SL93 Series Power Supply (#11-381)

Stock **#11-381** **20+ In Stock**

⊖ 1 ⊕ **\$980<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>\$980.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads



**General**

OEM **Type:**

[1135, 1135P](#) **Compatible Laser Models:**

SL93 Series **Model Number:**

[#62-726, #62-727](#) **Compatible Laser Stock Number:**

CDRH Delay (3-5 seconds) **Features:**

## Physical & Mechanical Properties

7.05 x 2.30 x 1.40  
Dimensions (inches):

## Electrical

20.15  
Output Power (W):

0.75 (Max. Current Draw)  
Input Current (A):

## Hardware & Interface Connectivity

3100  
Output Voltage (V):

6.5  
Output Current (mA):

High Voltage Alden Connector  
Connector:

100-250, 60/50Hz  
Input Voltage (V):

## Regulatory Compliance

[View](#)  
Certificate of Conformance:

## Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

**Note:** Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

## Technical Information

### Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

