

[See all 43 Products in Family](#)

Power Supply for 1.5-2.0mW HeNe Laser, 12 VDC, Bare Wire Leads



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock **#11-384** [CONTACT US](#)

-

1

+

S\$490⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$490.00 each
Need More?	Request Quote

Product Downloads



General

OEM

Type:

Compatible Laser Models:

[1101](#), [1101P](#), [1103](#), [1103P](#), [1122](#), [1122P](#)

L23 Series

Model Number:

Compatible Laser Stock Number:

[#62-718](#), [#62-719](#), [#62-720](#), [#62-721](#), [#64-103](#), [#64-104](#)

Features:

CDRH Delay (3-5 seconds)	
Physical & Mechanical Properties	
4.00 x 1.50 x 1.00	Dimensions (inches):
Electrical	
8.33	Output Power (W):
3 (Max. Current Draw)	Input Current (A):
Hardware & Interface Connectivity	
1700	Output Voltage (V):
4.9	Output Current (mA):
High Voltage Alden Connector	Connector:
10-14 DC	Input Voltage (V):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

