

Red Laser Pointer



Stock #53-546 3-5 DAYS

- 1 +

S\$40.60

ADD TO CART

Qty 1+
S\$40.60

Volume Pricing
Request Quote

Get Product Downloads



Output Power (mW):
5

Wavelength (nm):
650.00

Wavelength Tolerance (nm):
±10

Power Requirement:
2 AAA(not included)

Beam Diameter (mm):
3.175

Output Type: Free Space
Type of Laser: Diode
Laser Class - CDRH: 3R
Color: Red
Operating Lifetime (hours): 3.00
Length (mm): 133.35

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View
