

Right Angle Adapter (M46 x 0.75)



Right Angle Adapter (M46 x 0.75), #66-928

Stock #66-928 **12 In Stock**

⊖ 1 ⊕ **\$\$369⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	\$\$369.60 each
Need More?	Request Quote

Product Downloads

General

Lens Accessory **Type:**
Rotating **Type of Mount:**

Physical & Mechanical Properties

48 **Outer Diameter (mm):**
Black Anodized Ring **Construction:**

Optical Properties

Substrate: N-BK7
Wavelength Range (nm):
350 - 800

Coating:
Anti-Reflection Coating

Threading & Mounting

Filter Thread:
M46 x0.75

Mounting Threads:
Female Thread: M46 x0.75
Male Thread: M46 x0.75

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
[View](#)

Reach 242:
Compliant

Product Details

- Compatible with Filter Threads from M25.5 to M46
- Prism Faces are AR Coated While Side Faces are Ground and Blackened

The Right Angle Adapter features a prism design and housing with a M46 mount that easily adapts to lenses with threading ranging from M25.5 to M43 by means of a step ring (sold separately). Fully adjustable through 360° and includes a locking thumb screw to maintain the positioning of the assembly.

Technical Information

