

Right Angle Adapter (M46 x 0.75)



Right Angle Adapter (M46 x 0.75), #66-928

Stock **#66-928** 9 In Stock

-

1

+

S\$369⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$369.60 each
Need More?	Request Quote

Product Downloads

General	
Type:	
Lens Accessory	
Type of Mount:	
Rotating	
Physical & Mechanical Properties	
Outer Diameter (mm):	
48	
Construction:	
Black Anodized Ring	

Optical Properties	
N-BK7	Substrate: ☐
350 - 800	Wavelength Range (nm):
Anti-Reflection Coating	Coating:
Threading & Mounting	
M46 x0.75	Filter Thread:
Female Thread: M46 x0.75 Male Thread: M46 x0.75	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Product Details

- Compatible with Filter Threads from M25.5 to M46
- Prism Faces are AR Coated While Side Faces are Ground and Blackened

The Right Angle Adapter features a prism design and housing with a M46 mount that easily adapts to lenses with threading ranging from M25.5 to M43 by means of a step ring (sold separately). Fully adjustable through 360° and includes a locking thumb screw to maintain the positioning of the assembly.

Technical Information

