

SCHOTT BG25, 12.5mm Dia., 1mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-359** 3-5 DAYS

[Additional Bandwidths](#)

− 1 +

S\$59.45

ADD TO CART

Qty 1-10
S\$59.45
Qty 11+
S\$53.65
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
400.00

Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT BG25
Coating: Uncoated
Color: Blue-Violet
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 487
Thickness (mm): 1.00 ±0.1
Type: Bandpass Filter
Wavelength: UV-VIS
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--