

SCHOTT BG39, 12.5mm Dia., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-382** 3-5 DAYS

[Additional Bandwidths](#)

-

1

+

S\$59.45

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| S\$59.45                      |
| Qty 11+                       |
| S\$53.65                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Diameter (mm):  
12.50

Center Wavelength CWL (nm):  
507.00

|                                                            |
|------------------------------------------------------------|
| <b>Density (g/cm³):</b><br>2.74                            |
| <b>Glass/Filter Number:</b><br><a href="#">SCHOTT BG39</a> |
| <b>Coating:</b><br>Uncoated                                |
| <b>Color:</b><br>Blue-Green                                |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.54          |
| <b>Surface Quality:</b><br>60-40                           |
| <b>Transformation Temperature (°C):</b><br>322             |
| <b>Thickness (mm):</b><br>2.00 ±0.2                        |
| <b>Type:</b><br>Bandpass Filter                            |
| <b>Wavelength:</b><br>VIS                                  |
| <b>Bevel:</b><br>Protective as needed                      |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
|------------------------------------------------------------|