


SCHOTT BG40, 50mm Sq., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-422** 3-5 DAYS

- 1 +

S\$127.60

ADD TO CART

Qty 1-10
S\$127.60
Qty 11+
S\$113.10
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Center Wavelength CWL (nm): 514.00
Density (g/cm³):

2.74
Glass/Filter Number: SCHOTT BG40
Length (mm): 50.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.53
Surface Quality: 60-40
Transformation Temperature (°C): 313
Thickness (mm): 2.00 ±0.2
Type: Bandpass Filter
Wavelength: UV-Vis
Width (mm): 50.00
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View