

SCHOTT BG55, 150 x 150mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT BG Glass (glass color will vary by product specification)

Stock **#16-903** 3-5 DAYS

-

1

+

S\$716.30

ADD TO CART

Qty 1-10
S\$716.30
Qty 11+
S\$643.80
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
150.0 x 150.0 +3.0/-0.0

Density (g/cm³):
2.64

Glass/Filter Number:
[SCHOTT BG55](#)

Length (mm): 150.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.54
Transformation Temperature (°C): 453
Thickness (mm): 4.50 ±0.5
Type: Bandpass Filter
Wavelength: UV-VIS
Width (mm): 150.00
Edges: Break Edges
Reflection Factor P_d: 0.91

Regulatory Compliance

Certificate of Conformance: View
--