

SCHOTT BG61, 129 x 97mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT BG Glass (glass color will vary by product specification)

Stock **#16-905** 3-5 DAYS

-

1

+

S\$506.05

ADD TO CART

Qty 1-10
S\$506.05
Qty 11+
S\$440.80
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
129.0 x 97.0 +3.0/-0.0

Density (g/cm³):
2.81

Glass/Filter Number:
[SCHOTT BG61](#)

Length (mm): 129.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.53
Transformation Temperature (°C): 402
Thickness (mm): 4.50 ±0.5
Type: IR Cut-Off Filter
Wavelength: UV-VIS
Width (mm): 97.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
--