

SCHOTT BG64, 100 x 80mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT BG Glass (glass color will vary by product specification)

Stock **#16-908** CLEARANCE CONTACT US

− 1 +

S\$210.18

ADD TO CART

Qty 1+

S\$210.18

Volume Pricing

[Request Quote](#)

Get Product Downloads

Dimensions (mm):
100.0 x 80.0 +3.0/-0.0

Density (g/cm³):
2.78

Glass/Filter Number:
[SCHOTT BG64](#)

Length (mm):
100.00

Coating:

Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.53
Transformation Temperature (°C): 417
Thickness (mm): 4.50 ±0.5
Type: IR Cut-Off Filter
Wavelength: UV-VIS
Width (mm): 80.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
--