

SCHOTT BG7, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT BG Glass (glass color will vary by product specification)

Stock #16-895 3-5 DAYS

-

1

+

S\$382.80

ADD TO CART

Qty 1-10
S\$382.80
Qty 11+
S\$343.65
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.61

Glass/Filter Number:
[SCHOTT BG7](#)

Length (mm): 165.00
Coating: Uncoated
Color: Deep Blue
Index of Refraction n_d: 1.52
Transformation Temperature (°C): 468
Thickness (mm): 4.50 ±0.5
Type: Bandpass Filter
Wavelength: UV-VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
--