


SCHOTT KG1, 50mm Dia., 2mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock #19-336 3-5 DAYS

-

1

+

S\$116.00

ADD TO CART

Qty 1-10

S\$116.00

Qty 11+

S\$101.50

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00

Density (g/cm³):
2.53

Glass/Filter Number:
[SCHOTT KG1](#)

Substrate: Heat Absorbing Glass
Operating Temperature (°C): 300 Maximum
Coating: Uncoated
Index of Refraction n_d: 1.52
Surface Quality: 60-40
Transformation Temperature (°C): 599
Thickness (mm): 2.00 ±0.2
Type: IR Cut-Off Filter
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Wavelength Range (nm): 300 - 2700
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--