

SCHOTT OG590, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT OG Glass (glass color will vary by product specification)



Stock **#16-930** 3-5 DAYS

- 1 +

S\$381.35

ADD TO CART

Qty 1-10
S\$381.35

Qty 11+
S\$342.20

Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.56

Glass/Filter Number: SCHOTT OG590
Length (mm): 165.00
Coating: Uncoated
Color: Red
Index of Refraction n_d: 1.51
Transformation Temperature (°C): 506
Thickness (mm): 4.50 ±0.5
Type: Longpass Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
