

SCHOTT RG1000, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock #16-429 3-5 DAYS

- 1 +

S\$46.40

ADD TO CART

Qty 1-10
S\$46.40
Qty 11+
S\$40.60
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
1,000.00 ±6

Density (g/cm³):

2.73
Glass/Filter Number: SCHOTT RG1000
Coating: Uncoated
Color: Black
Passband Limit 1 λ_{p1} (nm): 1300
Index of Refraction n_d: 1.54
Spectral Transmittance t_p (%): 90
Stopband Limit λ_s(nm): 730
Surface Quality: 60-40
Transformation Temperature (°C): 476
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.91
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--