

SCHOTT RG665, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT RG Glass (glass color will vary by product specification)

Stock **#16-935** 3-5 DAYS

-

1

+

S\$381.35

ADD TO CART

Qty 1-10
S\$381.35
Qty 11+
S\$342.20
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.77

Glass/Filter Number:
[SCHOTT RG665](#)

Length (mm): 165.00
Coating: Uncoated
Color: Red
Index of Refraction n_d: 1.54
Transformation Temperature (°C): 527
Thickness (mm): 4.50 ±0.5
Type: Longpass Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.91

Regulatory Compliance

Certificate of Conformance: View
--