

SCHOTT RG9, 50mm Sq., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock #14-531 3-5 DAYS

- 1 +

S\$112.38

ADD TO CART

Qty 1-10
S\$112.38
Qty 11+
S\$110.20
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Cut-On Wavelength (nm):
726.00

Density (g/cm³):

2.58
Glass/Filter Number: SCHOTT RG9
Length (mm): 50.00
Coating: Uncoated
Color: Black
Index of Refraction n_d : 1.52
Surface Quality: 60-40
Transformation Temperature (°C): 519
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: IR
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View