

SCHOTT UG11, 50mm Sq., 1mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock #14-454 3-5 DAYS

-

1

+

S\$246.50

ADD TO CART

Qty 1-10
S\$246.50
Qty 11+
S\$220.40
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Center Wavelength CWL (nm): 325.00
Density (g/cm³):

2.92
Glass/Filter Number: SCHOTT UG11
Length (mm): 50.00
Coating: Uncoated
Color: Black
Index of Refraction n_d : 1.56
Surface Quality: 60-40
Transformation Temperature (°C): 545
Thickness (mm): 1.00 ±0.1
Type: Bandpass Filter
Wavelength: UV
Width (mm): 50.00
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View