

SCHOTT VG20, 12.5mm Dia., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock #16-381 3-5 DAYS

[Additional Bandwidths](#)

- 1 +

S\$68.15

ADD TO CART

Qty 1-10
S\$68.15
Qty 11+
S\$59.45
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Center Wavelength CWL (nm):
500.00

Density (g/cm³): 2.85
Glass/Filter Number: SCHOTT VG20
Coating: Uncoated
Color: Green
Index of Refraction n_d: 1.54
Surface Quality: 60-40
Transformation Temperature (°C): 390
Thickness (mm): 2.00 ±0.2
Type: Bandpass Filter
Wavelength: UV-VIS
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--