



SCHOTT VG9 50mm Sq., 1mm Thick Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock #14-442 3-5 DAYS

1

S\$127.60

ADD TO CART

Qty 1-10
S\$127.60
Qty 11+
S\$113.10
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Center Wavelength CWL (nm): 525.00
Density (g/cm³):

2.87
Glass/Filter Number: SCHOTT VG9
Length (mm): 50.00
Coating: Uncoated
Color: Green
Index of Refraction n_d: 1.55
Surface Quality: 60-40
Transformation Temperature (°C): 462
Thickness (mm): 1.00 ±0.1
Type: Bandpass Filter
Wavelength: VIS
Width (mm): 50.00
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
