

TECHSPEC[®] Sliding 2" x 3" Base Plate Slot



Stock **#52-083** 20+ In Stock

-

1

+

S\$35^{.35}

ADD TO CART

Volume Pricing	
Qty 1-9	S\$35.35 each
Qty 10+	S\$31.36 each
Need More?	Request Quote

Product Downloads

General

EnglishType:

Physical & Mechanical Properties

76.20Length (mm):

50.80Width (mm):

9.50Thickness (mm):

Black Anodized Aluminum	Construction:
2	Number of Slots:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Increase the Versatility of Existing Mounting Equipment
- Ideal for Direct Mounting to Standard Breadboards
- Counterbored 1/4-20 or M6 x 1.0 Holes/Slots

TECHSPEC® Slotted 2" x 3" Base Plates are versatile mounting surfaces for breadboard and optical rail applications. Three 6.4mm diameter counterbored holes, ideal for 1/4"-20 hardware, allow posts or post holders to be mounted directly and can also accommodate a variety of other optomechanical components. The plates are ideal for adding extra versatility and adjustment capability to a benchtop optical system. TECHSPEC® Slotted 2" x 3" Base Plates are available in standard sliding or side to side sliding configurations, allowing for adjustment along or perpendicular to the optical axis of the system.

Technical Information

