

Small X-Y Axis Leadscrew Drive



X-Y Axis Leadscrew Drive Metric Stages



Stock **#36-036** [CONTACT US](#)

⊖ 1 ⊕ **\$\$592²⁰**

ADD TO CART

Volume Pricing

Qty 1-9	\$\$592.20 each
Qty 10+	\$\$523.46 each
Need More?	Request Quote

Product Downloads

General

Metric **Type:**

Physical & Mechanical Properties

Linear (X-Y) **Type of Movement:**

Guide System:

Dovetail	
24 x 30	Stage Size (mm):
10 (±5)	Travel (mm):
5.8mm Thru	Center Hole:
Brass	Construction:
0.5	Leadscrew Pitch (mm):
3.5	Load Capacity (kg):
0.22	Weight (kg):

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
------------	-----------------------

Threading & Mounting

(6) M3 x 0.5	Mounting Threads:
--------------	--------------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- Locking Knobs for Secure Positioning
 - 0.5mm Travel per Knob Rotation
 - Available with up to 15mm Travel in X and Y with 12mm Travel in Z
- Leadscrew Drive Stages are ideal for a variety of positioning requirements that require high load capacities. Each stage features a leadscrew drive and locking knobs for securing the stage position. A top plate is available for large models (#58-290) with both M6 and 1/4-20 tapped holes to directly accept posts or post holders. Large models feature an aluminum base plate for easy integration.

Technical Information

