

[See all 19 Products in Family](#)

Smart Vision Lights 45mm Bar Light Mount



Stock #90-439 **NEW** 1 In Stock

- 1 + \$96.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	\$96.60 each
Need More?	Request Quote

Product Downloads

General

Model Number:
BKT0025

Manufacturer:
Smart Vision Lights LLC

Environmental & Durability Factors

Operating Temperature (°C):
-10° to +40°

Regulatory Compliance

Product Details

- Compact Bar Lights Available In 45mm Or 75mm Lengths
- Delivers up to 73,000 (for the 75mm) and 44,000 (45mm) lux with Strobing
- Available In White, Blue, Green, Red, Or IR Wavelengths
- Ideal For Space-Constrained Imaging Applications

Smart Vision Lights LMMini Bar Lights are compact linear lights that are designed to deliver intense light for space-constrained applications and feature IP65 rating for dust and water protection. These lights are available in 45 or 75mm lengths in white, blue (470nm), green (530nm), red (635), or IR (850nm) wavelengths. Built in Multi-Drive™ technology allows for these lights to operate in continuous mode for standard operation or strobe mode for high speed or increased brightness needs. Smart Vision Lights LMMini Bar Lights are recommended to use at a working distance of 100 – 1000mm. Optional mounting brackets are sold separately and can be used to configure the lights in a quad formation to illuminate a larger area.

;